

2-Chamber Incubators | Upper And Lower Chambers with Low Temp.

IQ823C

- Forced Convection
- Automatic Overheating Preventer
- Overheating Preventer
- Self-diagnostic Function
- Power Failure Compensation Function
- Overcurrent Leakage Circuit Breaker

Operating temp. range **-10~60°C** Temp. uniformity **±1.0°C (at 37°C)** Internal capacity **143L×2**

A two-chamber low-temperature incubator capable of independent program operation.

Features

- The controller panel is set on the door, improving operability.
- The process of incubation and preservation, etc., can log 6 programs from 10 segments to 30 segments according to experimental conditions.
- Defrosting can be set to cycle defrost based on the continuous operation time of the compressor. Both chambers are equipped with large cable ports with an internal diameter of 50mm.
- Equipped with safety functions such as refrigerator overload relay, independent overheat prevention device, overcurrent leakage protection switch, self-diagnosis circuit (temperature sensor abnormality, heater disconnection, SSR short circuit, automatic overheat prevention), buzzer alarm in case of abnormality, etc.
- Equipped with door lock.



Internal chamber




Cable port



Shelf



Heating and cooling curve



Specifications

Model		IQ823C	
System		Forced convection	
Performance	Operating temp. range	-10~60°C (both upper chamber and lower chamber)	
	GB standard	Temp. fluctuation	±0.3°C (at 37°C)
		Temp. uniformity	±1.0°C (at 37°C)
	Temp. arrival time	20°C→52°C≤30min	
	Temp. arrival time	20°C→4°C≤60min	
Composition	Interior material	Stainless steel (SUS304)	
	Exterior material	Cold rolled steel plate with chemical proofing coating	
	Insulating material	Foamed polystyrene	
	Refrigerator	158W×2	
	Refrigerant	R134A	
	Defrost mechanism	Cycle operation	
	Heater	Nickel-chromium alloy heating wire 550W×2	
Cable port	Inner diameter: 50mm (right side)		
Controllers	Temp. control method	PID control	
	Temp. setting method	Digital settings achieved via function menu key and ▲▼ keys	
	Temp. display method	Achieved temp. display:	Green 4-digit LED digital display
		Setting temp. display:	Red 4-digit LED digital display
	Timer	1 min~99 h 59 min and 100~999 h 50 min (including timer waiting function)	
	Operation functions	Fixed temp. operation, auto start, quick auto stop, auto stop, program operation, 3 modes (30 segments×1, 15 segments×2, 10 segments×3)	
Additional functions	Deviation correction, key lock, power outage compensation		
Safety device	Refrigerator overload relay, independent overheat prevention device, overcurrent leakage protection switch, self-diagnosis circuit (temperature sensor abnormality, heater disconnection, SSR short circuit, automatic overheat prevention), buzzer alarm in case of abnormality, etc.		
Specifications	Internal dimensions (W×D×H mm)	600×485×500 each	
	External dimensions (W×D×H mm)	710×656×1792	
	Internal capacity	143L×2	
	Shelf load	Approx. 15kg/shelf	
	Shelf layers/shelf support spacing	13 layers×2 chambers/30mm	
	Power supply (50Hz) rated current	AC220V 7A	
	Weight	Approx. 165kg	
Accessories	Shelf/supports	Stainless punching mesh plate: 2 chambers×3 pieces/2	
	Key	2 chambers×2 pieces	
Options	Shelves, micro printer, data logger, external communication function (RS485), temperature output terminal (4~20mA), external alarm output terminal, time arrival output terminal, centralized monitoring software, touch screen controller		

Sterilizers	1
Granulation and Spray Dryers	2
Furnaces	3
Ovens	4
Incubators	5
Plasma Equipment	6
Water Purifiers	7
Baths	8
Water Circulators	9
Rotary Evaporators	10
Stirrers & Shakers	11
Options	12